

Endy NT2 micromotor with integrated light



ARE YOU LOOKING FOR AN EFFICIENT DEVICE WITH AN OPTIMUM CONTROL ?

With Endy NT2,
you have a tailored solution offering autonomy and confort of use

a balanced compact motor with LED that can be autoclaved at 134°


The white LED under the contra-angle **illuminates the operating field without casting a shadow** or altering visibility.

a wide range of speeds with a single contra-angle

The Endy NT2 lets you set your file speed between 250 and 1200 revolutions per minute using the same contra-angle. **A single machine can suffice for widening all root canals.**

consistent torque and speed

The **speed** of the Endy NT2 **remains consistent regardless of the force with which the file is used in the root canal.** It never varies, even if the battery is less than 50% charged. The **torque is always controlled in order to preserve your files.**



Unit drawing

YOUR PARTNER FOR OVER 20 YEARS

Founded in 1993 and established in France in the Bordeaux region, **IONYX designs and manufactures specialized endodontic machines.** Aimed at general practitioners anxious to improve the quality of their treatments and the level of comfort they offer, **the entire IONYX range is conceived for simple, everyday use.**

Represented in many locations around the world thanks to its large network of distributors, **IONYX is a renowned specialist within the dental profession.**



Endy NT2 micromotor with integrated light

TECHNICAL CHARACTERISTICS

rapid motor shutdown

As soon as the programmed torque is achieved, the motor is quickly shut down by means of an electronic lock, limiting the risk of breakage of the instrument.

interruptible slow reverse

This 1-second slow-reverse technology used by IONYX since 1996, lets you remove the instrument without sending dental debris back towards the apex.

long Li-ion battery life

The Endy NT2 lets you work on battery power for 1 hour with an average torque of 1.5 N.cm (40 root canal treatments on average reported).

quick charger

The device's quick charger fully recharges your battery in 2 hours. Your battery is protected against short circuits or any heating during the charging process, ensuring complete safety. A red indicator light indicates that the battery is in safety lockout.

10-memory settings


The Endy NT2 has a 10-memory settings for programming as many torques and speeds corresponding to each of the files used. Programming is easy and straightforward.



side view




front view



Autoclavable LED drawing

*The Endy NT2 electronic casing has a 2-years warranty.
The contra-angle, the battery and the accessories have a 1-year warranty.*

Learn about the other products in our **ionyx** range



Locapex Five
apex locator

Endy 6200
micromotor with
apex locator



ionyx

34 rue de Fleurenne
F-33290 BLANQUEFORT

T. +33 5 56 35 34 27
F. +33 5 56 95 16 20

ionyx@ionyx.eu
www.ionyx.eu

