

Vitesse et couple préconisés par :
Speed and torque that are recommended by :

HERO 642



Endy 6200
micromotor and apex locator



Endo Master 2
Endy 6200 previous version

HERO 642 FILES	RPM	TORQUE N/CM
SEQUENCE 1 NARROW CANALS		
30/06	400	1.5
30/04	400	1
30/02	400	0.75
SEQUENCE 2 MEDIUM CANALS		
25/06	400	1.25
25/04	400	0.75
25/02	400	0.5
30/04	400	1
30/02	400	0.5
SEQUENCE 3 WIDE CANALS		
20/06	400	1.25
20/04	400	0.5
20/02	400	0.5
25/04	400	0.75
25/02	400	0.5
30/02	400	0.5

*Ces valeurs sont données à titre indicatives et ne peuvent en aucun cas engager la responsabilité de IONYX.
 These values are for information purposes only and cannot engage IONYX responsibility under no circumstance.*

**Your partner
 for over 25 years !**

