

Vitesse et couple préconisés par :
Speed and torque that are recommended by :

MTWO



Endy 6200
 micromotor and apex locator



Endo Master 2
 Endy 6200 previous version

MTWO FILES	RPM	TORQUE N/CM
SEQUENCE 1 NARROW CANALS		
10/04	300	0.5
15/05	300	0.5
20/06	300	0.75
25/06	300	1
25/07	300	2
SEQUENCE 2 MEDIUM CANALS		
30/05	300	1.25
35/04	300	1.25
40/04	300	1.5
20/15 A1	300	0.75
15/15 A2	300	0.75
25/20 A3	300	0.75
SEQUENCE 3 WIDE CANALS		
15/05 R	300	0.5
25/05 R	300	1
10/04	300	0.5
15/05	300	0.5
20/06	300	0.75
25/06	300	1

→ 25/07 option for vertical condensation

→ 15/05 R & 25/05 R for canal retreatment

Ces valeurs sont données à titre indicatives et ne peuvent en aucun cas engager la responsabilité de IONYX.
 These values are for information purposes only and cannot engage IONYX responsibility under no circumstance.

**Your partner
 for over 25 years !**

